







Rating	3A 125V AC, 1.5A 250V AC 	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1000V 1 minute		
Switch Function	2P SPST OFF-(ON)		



Material:
Housing: Black, Nylon#66
Button: Red, Nylon#66
Terminals: Silver plated, Copper Alloy



1、Tolerances ± 0.3 Unless Otherwise Specified

08/30/'21	趙恒鑫	依ECR(GLE20210820-109), 去除SCI LOGO					
Date	Name	Description					No.
Drawn	Checked	Approved	SCI BOM No.	1830774	Model Name	PUSH SWITCH	
趙恒鑫	符列迎	李生	Customer No.	112-R13-502A-R/B	Model No.	R13-502A	Rev.
08/30/'21	2021/09/03	2021/09/03	Unit	mm	 Shin Chin Industrial Co., Ltd.		1