







Rating	3A 125V AC, 1.5A 250V AC 	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1000V 1 minute		
Switch Function	2P SPST OFF-(ON)		



Material: 
Housing: Metal, Cr-Plating
Button: Red, Nylon#66
Terminals: Silver Plated, Copper Alloy



1、Tolerances ± 0.3 Unless Otherwise Specified

05/29/'23	曾敏捷	依ECR(RAD20221214-567)設計變更					
09/01/'21	趙恒鑫	依ECR(GLE20210820-109), 去除SCI LOGO					
Date	Name	Description				No.	
Drawn	Checked	Approved	SCI BOM No.	1830747	Model Name	PUSH SWITCH	
曾敏捷	孫列迎	李理	Customer No.	112-R13-502MA-R/B	Model No.	R13-502MA-05	Rev.
05/29/'23	2023/06/14	2023/06/14	Unit	mm	 Shin Chin Industrial Co., Ltd.		2