







Rating	3A 125V, 1.5A 250V AC	Mounting Hole 	Circuit Diagram 
Contact Resistance	50m ohm Max		
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1000V 1 minute		
Operation Temperature	0°~85°		
Switch Function	3P SPDT ON-(ON)		



Material: 
Frame: Metal, Cr-Plating
Actuator: Black, Nylon#66
Terminals: Copper Alloy



Tolerances ± 0.3 Unless Otherwise Specified

06/27/'23	曾敏捷	依 ECR(RAD20230307-067) 設計變更					
09/02/'11	雷云飛	Updated on the mark bottom					
Date	Name	Description				No.	
Drawn	Checked	Approved	SCI BOM No.	1830997	Model Name	PUSH SWITCH	
曾敏捷	符列亞	李理	Customer No.	112-R13-502MC-B/B	Model No.	R13-502MC-05	Rev.
06/27/'23	2023/07/13	2023/07/13	Unit	mm	 Shin Chin Industrial Co., Ltd.		2