




Rating	6A 14V DC	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-20°C~85°C		
Switch Function	4P SPST OFF-ON (LED independent)		

Material:
Frame: Nylon#66+33%GF, Black
Actuator: Red clear, PC
LED: Red
Printed: None



Tolerances ± 0.3 Unless Otherwise Specified

C8/R13/R13-508BL-05

									△
									△
Date	Name	Description							NO
Drawn	Checked	Approved	SCI BOM NO.	1831620	Model Name	PUSH SWITCH			
林珮呈			Customer No.	112-R13-508BL-BRR12V	Model No.	R13-508BL-05	Rev.		
4/29/19			Unit	mm	Shin Chin Industrial Co., Ltd.				0