








Rating	3A 125V AC, 1.5A 250V AC 	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1000V 1 minute		
Switch Function	2P SPST OFF-(ON)		



Material:
Housing: Black,Nylon#66
Button: Black,Nylon#66
Terminals: Silver plated ,Copper alloy



1、Tolerances ± 0.3 Unless Otherwise Specified

								
08/30/'21	趙恒鑫	依ECR(GLE20210820-109),去除SCI LOGO						
Date	Name	Description						NO
Drawn	Checked	Approved	SCI BOM NO.	1830746	Model Name	PUSH SWITCH		
趙恒鑫	孫列迎	李理	Customer No.	112-R13-510A-B	Model No.	R13-510A-05	Rev.	
08/30/'21	2021/09/03	2021/09/03	Unit	mm	 Shin Chin Industrial Co., Ltd.			1