







Rating	3A 125V AC , 1.5A 250V AC	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Switch Function	2P SPST OFF-(ON)		



Material:
Frame: Nylon#66+33%GF, Black
Actuator: Nylon#66, Red
Terminals: Silver Plated Brass
Printed: None



Tolerances Unless Otherwise Specified ± 0.3

									△
									△
Date	Name		Description						No.
Drawn	Checked	Approved	SCI BOM No.	1830235	Model Name	PUSH SWITCH			
曹盈芳		王佰山	Customer No.	112-R13-511A-R	Model No.	R13-511A-05			Rev.
06/01/16		6/1/16	Unit	mm	Shin Chin Industrial Co., Ltd.				0