




Rating	3A 125V AC 1.5A 250V AC		Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.			
Insulation Resistance	DC 500V 100M ohm Min.			
Dielectric Strength	AC 1500V 1 minute			
Operation Temperature	-20°C~85°C			
Switch Function	2P SPST OFF-(ON)			

Material:
Frame: Black, Nylon#66
Actuator: White, PC
Terminals: Copper Alloy



Tolerances ± 0.3 Unless Otherwise Specified

08/22/12	柳新強	依BOM修正圖面，去掉LED端子，且增加 SCI LOGO				△	
Date	Name	Description				No.	
Drawn	Checked	Approved	SCI BOM No.	1831050	Model Name	PUSH SWITCH	
柳新強	符元迎	Simon	Customer No.	112-R13-523A-05-BW	Model No.	R13-523A-05	Rev.
08/22/12	8/23/12	9/3/12	Unit	mm	Shin Chin Industrial Co., Ltd.		1