








Rating	3A 125V AC 1.5A 250V AC		Mounting Hole	Circuit Diagram	
Contact Resistance	50m ohm Max.			OFF	
Insulation Resistance	DC 500V 100M ohm Min.			ON	
Dielectric Strength	AC 1500V 1 minute				
Operation Temperature	-20° C~85° C				
Switch Function	4P SPST OFF-ON(LED independent)				



Material:
Frame: Nylon#66, Black
Actuator: PC, Red
LED Color: Red
Terminals: Copper Alloy



Tolerances ± 0.3 Unless Otherwise Specified

Date	Name	Description						No.	
Drawn	Checked	Approved	SCI BOM No	1831200	Model Name	PUSH SWITCH			
曾敏捷			Customer No	112-R13-523BL-R-12V	Model No.	R13-523BL-05	Rev.		
07/12/18	7/12-18	7/12-18	Unit	mm	Shin Chin Industrial Co., Ltd.				0