







Rating	1A 125VAC/ 0.5A 250VAC	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1000V 1minute		
Switch Function	2P SPST OFF-(ON) (LED)		
		THICKNESS	0.5~2.0mm

*MATERIAL:
Frame: Black, PA#66+5%G
Actuator: Red, PC
Printed: None



C8\R13\R13-529AL-05(1830803)

Date	Name	Description							NO
Drawn	Checked	Approved	SCI BOM NO.	1830803	Model Name	PUSH SWITCH			
曹 盈 芳	王 佰 山	李 景 煌	Customer No.	112-R13-529AL-BRR	Model No.	R13-529AL-05			REV.
02/17/'09	02/18/'09	02/19/'09	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.				0