



Rating	16A 125VAC 1/3HP 10A 250VAC 1/2HP		Mounting Hole		Circuit Diagram			
	16(4)A 125/250Vac						T85	
	10A 125VAC, 6A 250VAC							
Contact Resistance	50m ohm Max.							
Insulation Resistance	DC 500V 100M ohm Min.							
Dielectric Strength	AC 1500V 1 minute							
Operation Temperature	-25°C~85°C	Thickness	X	Y				
		0.75...1.25	19.2-0.1	13.2+0.1				
		1.25...2	19.4-0.1	13.2+0.1				
Switch Function	3P SPDT ON-OFF-ON	2...3	19.8-0.1	13.2+0.1				


Material:

Frame: Nylon#66, Black



Actuator: Nylon#66, Black

Terminal: Cooper Alloy, Silver plating

Printed: White, hot stamping



Tolerances $\pm 0.3\text{mm}$ Unless Otherwise Specified

04/29/'22	曾敏捷	依ECR(JHF20220225-009)修改CQC安規標示				
2/23/'22	林珮呈	據ECR#RAD20210518-244之品管要求，去除VDE安規，更新DEMKO/ENEC 15安規				
07/02/'14	黃洋	依實物增加SCI LOGO,更新圖面.				
11/16/'10	曹盈芳	本體刻字更新, 重新出圖				
Date	Name	Description				NO
Drawn	Checked	Approved	SCI BOM NO.	1820407	Model Name	ROCKER SWITCH
曾敏捷			Customer No.	112-R13-66D	Model No.	R13-66D-02
04/29/'22	2022/06/15	2022/06/15	Unit	mm	 Shin Chin Industrial Co., Ltd.	
						Rev. 4