



Rating	30A
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1000V 1 minute
Operation Temperature	-20°C~+65°C
Color	Black(-)

*Material:
 Handle: PVC
 Clip: Nickel plated steel
 *Jaw opens: 13mm max



								△
								△
Date	Name		Description					NO
Drawn	Checked	Approved	SCI BOM No.	1530064	Model Name	BATTERY CLIPS		
柳新強		<i>Shin</i>	Customer No.	112-R8-110	Model No.	R8-110		Rev.
11/25/13		<i>1/10-14</i>	Unit	mm	Shin Chin Industrial Co., Ltd.			0