


Test Voltage Range	5V~30V DC
Insulation Resistance	DC 500V 100M Ω Min
Dielectric Strength	AC 1500V 1 Second
Operating Temperature	-0°C~+60°C



UL1803 24AWG 紅/黑色 L(Including Clamp)=622±30 mm



A4

									△
									△
Date	Name	Description							NO
Drawn	Checked	Approved	SCI BOM No.	15 70283	Model Name	Battery Tester			
胡朝鈺		<i>D.L.</i>	Customer No.	112-R8-124	Model No.	R8-124			REV.
2008/5/20		5/20/08	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.				1