


Rating	3A
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	-20°C~+80°C
Color	Red

*Material:
Handle: ABS.
Clip: Phosphor bronze.
*Fits $\phi 2\text{mm}$ tip plug .



									△
									△
Date	Name		Description						NO
Drawn	Checked	Approved	SCI BOM No.	1510050	Model Name	IC Clip			
袁浩徐		<i>Smice</i>	Customer No.	112-R8-16E-R	Model No.	R8-16E			Rev.
06/17/20		<i>6/17-20</i>	Unit	mm	Shin Chin Industrial Co., Ltd.				0