


Rating	300mA
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	-20°C~+80°C
Color	Black

*Material:
 Handle: ABS.
 Clip: Phosphor bronze.
 *Fits O.D. less than $\phi 2\text{mm}$ wire by soldering.



								△
								△
Date	Name	Description						No.
Drawn	Checked	Approved	SCI BOM No.	1510051	Model Name	IC CLIP		
柳新強		<i>Shin</i>	Customer No.	112-R8-16F-B	Model No.	R8-16F		Rev.
11/09/13		11/9-13	Unit	mm	Shin Chin Industrial Co., Ltd.			0.