




Rating	3A
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	-20°C~+80°C

Material:
 Handle: ABS, Red. \triangle
 Clip: Nickel plated brass.
 Alligator clip with $\phi 4.0$ mm socket.
 Jaw opens: 6mm max.



C8/R8/R8-1A

								\triangle
3/9/18	林玗呈	修正材質說明：Handle: ABS, Rad.改為 Red						\triangle
Date	Name	Description						NO
Drawn	Checked	Approved	SCI BOM No.	1530007	Model Name	ALLIGATOR CLIPS		
林玗呈		王偉	Customer No.	112-R8-1A-R	Model No.	R8-1A		Rev.
3/9/18		3/9/18	Unit	mm	Shin Chin Industrial Co., Ltd.			1