


Rating	10A
Insulation Resistance	DC 500V 100M ohm Min.
Voltage Breakdown	AC 500V 1 minute
Operation Temperature	-20°C~80°C
Color	Red

Material:
Metal Clip: nickel plated SPCC
Plastic Cover: PVC , Red

*.Clamping force 2.5kgf at 8 mm(A)

*.Clamping force 300g±50g when clamped 12 AWG wire



Tolerances Unless Otherwise Specified ± 0.5

									△
									△
Date	Name			Description					NO
Drawn	Checked	Approved	SCI BOM No.		Model Name	ALLIGATOR CLIPS			
林珮呈			Customer No	112-R8-91-R	Model No.	R8-91		Rev.	X0
4/29/'19			Unit	mm	Shin Chin Industrial Co., Ltd.				