




Rating	See Table	Mounting Hole	Circuit Diagram
Insulation Resistance	DC 500V 100MΩ Min		
Dielectric Strength	AC 500V 1Minute		
Operation Temperature	-25°C~+80°C		



LED Color	Lens Color	VF			IF	Viewing Angle	Mcd
		Min.	Typ.	Max.			
White	White Diffused	2.8V	3.6V	3.8V	20mA	30°	700~900

Material  
Housing: Cr Plated Brass
Bottom: Rubber



Remark:

1. LED Type: Ø3mm
2. Tolerances ±0.2 Unless Otherwise Specified

07/17/'19	袁浩徐	本體材質鋁改銅					
01/25/'19	袁浩徐	本體材質銅改鋁					
Date	Name	Description					No.
Drawn	Checked	Approved	SCI BOM No.	1720304	Model Name	LED Indicator Light	
袁浩徐			Customer No.	358-R9-103L-12-WD	Model No.	R9-103L-12-WD	Rev.
07/17/'19			Unit	mm	 Shin Chin Industrial Co., Ltd.		2