





Rating		See Table					Mounting Hole	Circuit Diagram
Insulation Resistance		DC 500V 100MΩ Min						
Dielectric Strength		AC 500V 1Minute						
Operation Temperature		-25°C~+80°C						
LED Color	Lens Color	VF			IF	Viewing Angle	Mcd	
		Min.	Typ.	Max.				
Yellow	Yellow Diffused	1.8V	2.0V	2.45V	20mA	50°	30	

Material  
Housing: Cr Plated Brass
Bottom: Rubber



Remark:

1. LED Type: $\varnothing 3\text{mm}$
2. Tolerances ± 0.2 Unless Otherwise Specified

07/17/'19	袁浩徐	本體材質鋁改銅					
01/25/'19	袁浩徐	本體材質銅改鋁					
Date	Name	Description					No.
Drawn	Checked	Approved	SCI BOM No	1720279	Model Name	LED Indicator Light	
袁浩徐			Customer No	358-R9-103L-12-YD	Model No.	R9-103L-12-YD	Rev.
07/17/'19		7/18-'19	Unit	mm	 Shin Chin Industrial Co., Ltd.		2