




Rating		12V DC			Mounting Hole	Circuit Diagram
Insulation Resistance		DC 500V 100M Ohm Min				
Dielectric Strength		AC 500V 1Min.				
LED Color	VF	IF	Iv(mcd)	View Angle		
Green	2.0V	20mA	66	80°		



Material
Housing: PC, Green

for 玖新 only

Unless otherwise specified all tolerances to be $\pm 0.3\text{mm}$.

C8\R9\R9-120L1-11-GG3(1720545)_1

						△	
05/11/'11	曹盈芳	依MCN#GRD2010085更正六角螺母				△	
Date	Name	Description				NO	
Drawn	Checked	Approved	SCI BOM No.	1720545	Model Name	LED Indicator	
曹盈芳		王佰山	Customer No.	358-R9-120L1-11-GG3	Model No.	R9-120L1-11-GG3	Rev.
05/11/'11		05/11/'11	Unit	mm	Shin Chin Industrial Co., Ltd.		1