




Rating		12V DC				Mounting Hole	Circuit Diagram
Insulation Resistance		DC 500V 100MΩ Min					
Dielectric Strength		AC 500V 1 minute					
Operation Temperature		-20° C ~ +85° C					
LED Color	LED Lens Color	VF	IF	Iv(mcd)	View Angle	Material:	
Yellow	Yellow Diffused	2.1V	20mA	50	30°		

Material:
 Body: Cr-Plated, Aluminum Alloy 
 Base: PF, Black
 Terminal: Nickel Plated Brass



Label:  R9-87L 12VDC

Tolerances Unless Otherwise Specified ±0.3mm

10/20/20	袁浩徐	本體材質銅改鋁					△
Date	Name	Description					No.
Drawn	Checked	Approved	SCI BOM No.	1720109	Model Name	LED INDICATOR	
袁浩徐			Customer No.	358-R9-87L-01-YD-12V	Model No.	R9-87L-01	Rev.
10/20/20		10/20/20	Unit	mm	 Shin Chin Industrial Co., Ltd.		1