







Pushbutton Units and Indicator Lights

30 mm Heavy Duty, Watertight/Oiltight, Class 52

• Revised •
03/20/2012

Accessories and spare parts

Selection and ordering data










| | Version | Suitable for | Color | Order no. | List Price \$ |
|---|--|--|--|--|---------------|
|  | Flush actuator lens cap | For flush type, non-illuminated pushbuttons bag of 20 caps | black red green yellow blue gray orange kit- all colors | 52RA1A1 52RA1A2 52RA1A3 52RA1A4 52RA1A5 52RA1A6 52RA1A8 52RA1AN | |
|  | Extended actuator lens cap | For extended type, non-illuminated pushbuttons bag of 20 caps | black red green yellow blue gray orange 1 of each color cap | 52RA1B1 52RA1B2 52RA1B3 52RA1B4 52RA1B5 52RA1B6 52RA1B8 52RA1BN | |
|  | Mushroom head cap - Plastic | For large 2 1/2" (63.5mm) type, set screw non-illuminated mushroom pushbuttons For small 1 5/8" (41.3mm) type, non-illuminated mushroom pushbuttons | black red green yellow blue gray orange 1 kit of each color cap black red green yellow blue gray orange 1 of each color cap | 52RB3E1 52RB3E2 52RB3E3 52RB3E4 52RB3E5 52RB3E6 52RB3E8 52RB3EN 52RB3D1 52RB3D2 52RB3D3 52RB3D4 52RB3D5 52RB3D6 52RB3D8 52RB3DN | |
|  | Mushroom head cap - Metal | For small 1 5/8" (41.3mm) type, set screw non-illuminated mushroom pushbuttons | chrome red green | 52RB3FC 52RB3F2 52RB3F3 | |
|  | Replacement Lens for Indicator Lights | For catalog numbers starting with 52PL or 52BL ^{①②} Plastic Glass | red green blue amber clear white 1 of each color red green blue amber clear white 1 of each color | 52RA4S2 52RA4S3 52RA4S5 52RA4S9 52RA4SA 52RA4SB 52RA4SN 52RA4T2 52RA4T3 52RA4T5 52RA4T9 52RA4TA 52RA4TB 52RA4TN | |
|  | Replacement Lens for Push to Test/Illuminated Pushbuttons | For catalog numbers starting with 52PT or 52BT ^③ Plastic | red green blue amber clear white | 52RA5S2 52RA5S3 52RA5S5 52RA5S9 52RA5SA 52RA5SB | |

① To order replacement lens for indicator lights starting with 52PA, 52PE, or 52PX, change the 6th digit to P for plastic and G for glass.

② It is possible to retrofit catalog numbers starting with 52PA, 52PE and 52PX with the replacement lens. The new lens have concentric ribs for improved light distribution.

③ To order replacement lens for push to test / illuminated pushbuttons starting with 52PA, 52PE, or 52PX, change the 6th digit to a P.

Selection and ordering data

| | Version | Suitable for | Color | Order no. | List Price |
|---|--|--|--|--|------------|
| | | | | | \$ |
| | Mushroom head push pull illuminated plastic | For small 1 3/4" type, push-pull units | red green amber | 52RC3JR 52RC3JS 52RC3JT | |
| | | For large 2 1/2" type, push-pull units | red green amber | 52RC3KR 52RC3KS 52RC3KT | |
|  | Mushroom head push pull illuminated metal | Chrome, for small 1 3/4" type, push-pull units | red green amber white | 52RB3H2 52RB3H3 52RB3H9 52RB3HB | |
|  | | BlackMax, for small 1 3/4" type, push-pull units | red green amber white | 52RX3H2 52RX3H3 52RX3H9 52RX3HB | |
|  | Mushroom head push pull non-illuminated plastic | For small 1 3/4" type, push-pull units (catalog numbers starting with 52PP or 52BP) ^① | black red green yellow blue gray orange 1 of each color | 52RC3D1 52RC3D2 52RC3D3 52RC3D4 52RC3D5 52RC3D6 52RC3D8 52RC3DN | |
|  | | For large 2 1/2" type, push-pull units (catalog numbers starting with 52PP or 52BP) ^① | black red green yellow blue gray orange 1 of each color | 52RC3E1 52RC3E2 52RC3E3 52RC3E4 52RC3E5 52RC3E6 52RC3E8 52RC3EN | |
| | Mushroom head push pull non-illuminated metal | For small 1 3/4" type, push-pull units (catalog numbers starting with 52PP or 52BP) ^① | red green chrome | 52RC3F2 52RC3F3 52RC3FC | |
|  | Twist to release head illuminated plastic | For small twist to release units | red green amber | 52RC3RR 52RC3RS 52RC3RT | |
|  | Twist to release head non-illuminated plastic | For small twist to release units | red green yellow | 52RC3R2 52RC3R3 52RC3R4 | |
|  | Replacement lens kit for illuminated selector switches (Knob with Insert) | | red green blue amber clear white | 52RA6P2 52RA6P3 52RA6P5 52RA6P9 52RA6PA 52RA6PB | |
|  | Lever inserts Short lever | | red green yellow blue gray orange white | 52RA2A2 52RA2A3 52RA2A4 52RA2A5 52RA2A6 52RA2A8 52RA2AB | |
|  | Long lever | | red green yellow blue gray orange white | 52RA2B2 52RA2B3 52RA2B4 52RA2B5 52RA2B6 52RA2B8 52RA2BB | |

① For push-pull units whose catalog numbers that start with 52PX, 52PA or 52PE, replacement heads are available. Order from the 52RB type "Mushroom head pushbutton cap" section on page 10/158.











Pushbutton Units and Indicator Lights

30 mm Heavy Duty, Watertight/Oiltight, Class 52

• Revised •
03/20/2012

Accessories and spare parts

Selection and ordering data

| | Version | Suitable for | Color | Order no. | List Price |
|---|--|---|---|--|------------|
| | | | | | \$ |
|  | Protective boot Offers protection from ice and foreign substances from interfering with button operation | Flush pushbutton operations | clear black | 52AABA 52AAB1 | |
|  | Guards Prevents accidental operation | Non-illuminated basic pushbuttons 1 5/8" mushroom pushbuttons, 1 3/4" push-pull units ^① , and twist to release units Push to test/illuminated pushbutton and indicator lights | chrome blackmax chrome blackmax chrome blackmax | 52AAGP 52AXGP 52AAGM 52AXGM 52AAGL 52AXGL | |
|  | EMERGENCY-STOP Lock Out EMERGENCY-STOP Backing Ring | Class 52 Illuminated Mushroom Head Pushbuttons; 304 Stainless Steel Yellow 90mm E-STOP Backing Ring | chrome (304 SS) | 52AALE 52AAR | |
|  | Locknuts Replacement front ring | Non-illuminated basic pushbuttons Non-illuminated mushroom pushbuttons Push-pull and twist-to-release units (only for push-pull units starting with 52PP or 52BP) ^② Indicator Lights Selector switches | chrome blackmax chrome blackmax chrome blackmax blue amber chrome blackmax | 52AANP 52AXNP 52AANL 52AXNL 52CANP 52CXNP 52AANL 52AXNL 52AANS 52AXNS | |
| Mounting Accessories | | Class 52 Trim Washer Kit (Set of 10 pcs) Class 52 Washer Kit (Include 2-Neoprene Gaskets, 1-Trim Washer, 1-Index Locking Ring (chrome)) | chrome | 52AAQ 52AAD | |
| Padlock attachments | | Non-illuminated basic pushbuttons | flush extended | 52AALA 52AALB | |
|  | Padlock cover Lock devices in off position | Pushbuttons, selector switches, and non-illuminated mushroom heads | | 52AALS | |
|  | Lock nut wrench | All devices | | 52MAWB | |
|  | Hole plugs | | corrosion resistant steel, grey stainless steel | 52AAH6 52ABH6 52ABHS | |
| Spare keys (Kit includes 1 Key) | | Class 52 Standard Keyed Selector Switch. Keyed Selector Switch ordered with Suffix X302. Keyed Selector Switch ordered with Suffix X301. Keyed Selector Switch ordered with Suffix X300. Keyed Selector Switch ordered with Suffix X299. Keyed Selector Switch ordered with Suffix X298. | 501CH 506CH 547CH 548CH 549CH 550CH | 52KEY-501CH 52KEY-506CH 52KEY-547CH 52KEY-548CH 52KEY-549CH 52KEY-550CH | |
| Grounding kit | | All devices | | 52AL109145 | |
|  | Touchsafe contact blocks with gold flashing 52 BAJ 1 NO 1 NC 1 NO - 1 NC | closes before 52BAK opens after 52BAJ Reed switch; UL listed for class 1 division 2; .25A Max, 200V AC, 10 Watt max .5A Max, 200V DC, 10 Watt max | | 52BAK 52BAJ ^④ 52BJK ^④ | |
|  | 52 BAK 1 NO early make 1 NC late break 1 NO - 1 NC | | | 52BAH 52BAE 52BAR ^③ | |
|  | 1 NC extra late break | | | 52BAU | |
| 52 BAR | | | | | |

① These can also be used with the 1 5/8" push-pull devices.

② For push-pull units starting with part numbers 52PA, 52PE or 52PX, replacement locknuts can be ordered using 52AANL (Chrome) and 52AXNL (BlackMax).

③ Hermetically Sealed

④ ⊕ Positive opening according to IEC 60947-5-1, Appendix K.


• Revised •
03/20/2012

Pushbutton Units and Indicator Lights

30 mm Heavy Duty, Watertight/Oiltight, Class 52

Accessories and spare parts

Selection and ordering data

| Version | Suitable for | Lamp voltage | Color | Order no. | List Price |
|---|--|--------------------------|--|--|------------|
| | | | | | \$ |
| Lamps with screw connection, miniature bayonet (BA 9s style) | | | | | |
|  | Incandescent lamps, | | | | |
| | Flashing, type 267 lamp (replaces 755 lamp) | 51, 52 | 6 V | 52AABNF | |
| | 6V type 755 lamp (Rated 150 mA) | 51, 52 | 6 V | 52AABN | |
| | 12V type 756 (Rated 80 mA) | 51, 52 | 12 V | 52AACN | |
| | 24V type 757 (Rated 80 mA) | 51, 52 | 24 V | 52AADN | |
| | 48V, 2W | 52 | 48 V | 3SB1902-1AP | |
| | 60V, 2W | 52 | 60 V | 3SR9424 | |
| | 120V, 2.5W, type #120MB (Rated 250 mA) | 52 | 120 V | 52AAENC1 | |
| | Neon (uses resistors) type B2A (NE-51H) | 52 | 120 V | 52AAPN | |
| | Candelabra, 120V, 3W, Full voltage type 3S6/5 | 52 older revision styles | 120 V | 52AAENC | |
| LED bulbs | | | | | |
| | LED, BA9s type (Rated 15 mA) | Class 52 | 6 V AC 24 V AC/DC 120 V AC | 52AEB□ 52AED□ 52AEE□ | |
| | LED, cluster type (Rated 0.5W) | Class 52 | 6 V AC 24 V AC 120 V AC 120 V DC | 52AEB□7 52AED□7 52AEE□7 52AEV□7 | |
| LED lighting module with integrated LED. | | | | | |
| | Single LED (Rated 35 mA Maximum) | Class 52 | 24 V AC/DC 120 V AC 240 V AC | 52AAIL□ 52AAIM□ 52AAIN□ | |
| Full voltage lighting module accessory with BA9s type lamp | | | | | |
| | Single LED | Class 52 | 6 V AC 24 V AC/DC 120 V AC | 52AAFB□B 52AAFD□B 52AAFE□B | |
| | Cluster LED | Class 52 | 6 V AC 24 V AC 120 V AC | 52AAFB□Y 52AAFD□Y 52AAFE□Y | |
| | Incandescent bulb | Class 52 | 6 V AC/DC 24 V AC/DC 120 V AC | 52AAFB 52AAFD 52AAFE | |
| Transformer lighting module accessory with BA9s type lamp | | | | | |
| | Single LED | Class 52 | 120 V AC 240 V AC 480 V AC 600 V AC | 52AATG□B 52AATH□B 52AATJ□B 52AATK□B | |
| | Cluster LED | Class 52 | 120 V AC 240 V AC 480 V AC 600 V AC | 52AATG□Y 52AATH□Y 52AATJ□Y 52AATK□Y | |
| | Incandescent bulb | Class 52 | 120 V AC 240 V AC 480 V AC 600 V AC | 52AATG 52AATH 52AATJ 52AATK | |

Technical Specifications
on page 10/169A

Color options:

- red
- green
- yellow/amber
- blue
- white/clear

2
3
4
5
B

**Note: Cluster LED only available in red, green and yellow