

623-0326-H3 Specification

► Mechanical

- Typical Application: LGA
- Pitch Range (minimum): 0.5 mm
- Work Force: 25.3 gf @ 0.38 mm travel
- Recommended Travel: 0.38 mm
- Temperature: -55 ~ 150°C
- Tip Device Side: Spear
- Tip PCB Side: Radius

► Electrical

- Self Inductance: 1.12 nH
- Mutual Capacitance: 0.30 pF
- Bandwidth @ -1 dB: 20 GHz
- Contact Resistance: < 55 mΩ
- Current Carrying Capability: 4.0A

► Plating

- Plunger Top: Homogenous alloy
- Plunger Bottom: Gold plated
- Barrel: Gold plated
- Spring: Gold plated

