



NOTES:

1. PLUG FINGER SAME AS 270
2. PLUG FINGER, HANDLE, AND STRAIN RELIEF SHIPPED UNASSEMBLED.
3. ASSEMBLE STRAIN RELIEF TO HANDLE BEFORE INSERTING CABLE.
4. THIS PRODUCT IS RoHS COMPLIANT.

PARTNUMBER	PART REV	RECOMMENDED STRAIN RELIEF CABLE RANGE
270F	0A	Ø 0.220 - Ø 0.190
270FL	0A	Ø 0.250 - Ø 0.220

CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
						SIZE *	WIDTH *	MULT *	LBS/M *	TEMPER *
						FINISH *			MATERIAL *	
						SPEC No. *			SPEC No. *	
						FIRST USED ON *		SCALE 5:4		<div>Switchcraft®</div>
						DATE DRAWN	BY	CHKD	APVD	
0A	PRELIMINARY	6/19/17	*	*		6/19/17	AB	AB	*	
							6/19/17	*		
REV	ECO NUMBER	DATE	BY	APVD						
REVISIONS					DO NOT SCALE DRAWING	NAME 270 FLEX, RoHS			PART No. 270F - 270FL	REV 0A

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]
- TWO PLACE DECIMALS ±0.02 [0.5]
- THREE PLACE DECIMALS ±0.005 [0.13]

DO NOT SCALE DRAWING

SolidWorks CAD File

