






NOTES:

- 1. PLUG FINGER SAME AS 297
- 2. PLUG FINGER, HANDLE, AND STRAIN RELIEF SHIPPED UNASSEMBLED.
- 3. ASSEMBLE STRAIN RELIEF TO HANDLE BEFORE INSERTING CABLE.
- 4. THIS PRODUCT IS RoHS COMPLIANT.

PARTNUMBER	PART REV	RECOMMENDED STRAIN RELIEF CABLE RANGE
297F	0A	Ø 0.220 - Ø 0.190
297FL	0A	Ø 0.250 - Ø 0.220

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
						SIZE *	WIDTH *	MULT *	LBS/M *	TEMPER *	
						FINISH *			MATERIAL *		
						SPEC No. *			SPEC No. *		
						FIRST USED ON *		SCALE 5:4		Switchcraft®	
0A	PRELIMINARY	6/19/17	*	*		DATE DRAWN 6/19/17	BY AB	CHKD AB 6/19/17	APVD *		
						SHEET 1 OF 1					
REV	ECO NUMBER	DATE	BY	APVD		NAME		PART No.		REV	
REVISIONS						DO NOT SCALE DRAWING		297 FLEX, RoHS		297F - 297FL	0A

DO NOT SCALE DRAWING