




LOC		DIST		REVISIONS					
A1			-	F	LTR	DESCRIPTION	DATE	DWN	APVD
				A3	NEW	PRO-E DRAWING / ECR-09-003111	05MAR2009	SR	AR
				A4	ECR-15-000844		29JAN2015	GSK	MKO



NOTES

- 1 PART SHALL BE FREE AND CLEAN OF BURRS AND
OTHER FOREIGN MATERIAL
- 2 PACKAGING: QUANTITY 2 PIECES
- 3 VARNISHING INSIDE HOUSING NOT REQUIRED

- 2 PACKAGING: QUANTITY 2 PIECES

- 3 VARNISHING INSIDE HOUSING NOT REQUIRED

2		CLIP BOLT	STAINLESS STEEL	BLANC		15	
1		CYLINDER SCREW	STAINLESS STEEL	BLANC		14	M5x16
	1	CYLINDER SCREW	STEEL	ZINC PLATED	BLUE	13	M5x16
1		LEG SPRING	STAINLESS STEEL	BLANC		12	
	1	LEG SPRING	STEEL	ZINC PLATED	BLUE	11	
1		RIVET PIN	STAINLESS STEEL	BLANC		10	5x80
	1	RIVET PIN	STEEL	ZINC PLATED	BLUE	9	5x80
1		COVER	ALUMINIUM	ALUMINIUM OXID	BLACK	8	
	1	COVER	ALUMINIUM		GREY	7	
2	2	SLOTTED PAN HEAD SCREW	STAINLESS STEEL	BLANC		6	M6x8
1		SIDE CLIP	STAINLESS STEEL	BLANC		5	
	1	SIDE CLIP	STEEL	ZINC PLATED	BLUE	4	
1	1	PROFIL SEAL	NEOPRENE		BLACK	3	
1		SURFACE MOUNTED HOUSING SIDE ENTRY	ALUMINIUM	ALUMINIUM OXID	BLACK	2	
	1	SURFACE MOUNTED HOUSING SIDE ENTRY	ALUMINIUM		GREY	1	
2-2	1-2	DESCRIPTION	MATERIAL	SURFACE	COLOR	ITEM	NOTES
HB.48.SGD-LB.2.36.Z							
HB-K.48.SGD-LB.2.36.Z							

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03FEB2009 R. SCHNEIDER CHK 03FEB2009 T. SCHNURPFIL		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1°		NAME SURFACE MOUNTED HOUSING SIDE ENTRY HB.48.SGD-LB.2.36-Z	
		APVD - PRODUCT SPEC - APPLICATION SPEC -		SIZE A1	
MATERIAL -		FINISH -		CASE CODE 00779	
		WEIGHT -		DRAWING NO C=1107007	
		CUSTOMER DRAWING		SCALE 5:1 SHEET 1 OF 1 REV A4	