

PZ 2.5 S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	0.14mm ² , 2.5mm ² , Trapezoidal crimp
Order No.	2903690000
Type	PZ 2.5 S
GTIN (EAN)	4099986027008
Qty.	1 pc(s).

PZ 2.5 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	31 mm	Depth (inches)	1.22 inch
Height	70 mm	Height (inches)	2.756 inch
Width	160 mm	Width (inches)	6.299 inch
Net weight	290.6 g		

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Description of contact

Conductor cross-section, max. AWG	AWG 14	Conductor cross-section, min. AWG	AWG 26
Crimping range, max.	2.5 mm ²	Crimping range, min.	0.14 mm ²
Type of contact	Wire-end ferrules with/without plastic collars		

tool data crimping

Crimping type/profile	Trapezoidal crimp	Wire end ferrules cross-section, max.	2.5 mm ²
Wire end ferrules cross-section, min.	0.14 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21043811

Downloads

Catalogues	Catalogues in PDF-format
------------	--