

CA-T2WB-7.5M-22/3P-R-BBG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	AC charging cable, Plug type - charging point: free conductor end, Plug type - vehicle side: Type 2, Charging power, max.: 22 kW, Number of phases: 3, Rated current: 32 A, Cable length: 7.5 m, Cable type: regular
Order No.	2828220000
Type	CA-T2WB-7.5M-22/3P-R-BBG
GTIN (EAN)	4064675368632
Qty.	1 pc(s).

Creation date April 24, 2023 11:33:12 PM CEST

CA-T2WB-7.5M-22/3P-R-BBG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	6,500 g
------------	---------

Temperatures

Storage temperature	-40 °C...70 °C	Humidity at storage temperature	5 - 95% rel. humidity
Operating temperature	-30 °C...50 °C	Operating temperature, min.	-30 °C
Operating temperature, max.	50 °C		

Material data

Operating temperature, max.	50 °C	Operating temperature, min.	-30 °C
Storage temperature, max.	70 °C	Storage temperature, min.	-40 °C

System requirements

Type of communication to vehicle	Control Pilot (CP), Proximity Pilot / Plug Present (PP)
----------------------------------	---

Features

Protection degree	IP55 with protection cap
-------------------	--------------------------

Housing

Protection degree	IP55 with protection cap
-------------------	--------------------------

Approvals and norms

ROHS	Conform	Approvals	IEC 62196-1, IEC 62196-2, EN 50620
------	---------	-----------	---------------------------------------

Classifications

ETIM 6.0	EC002897	ETIM 7.0	EC002897
ETIM 8.0	EC002897	ECLASS 9.0	27-14-47-05
ECLASS 9.1	27-14-47-05	ECLASS 10.0	27-14-47-05
ECLASS 11.0	27-14-47-05	ECLASS 12.0	27-14-47-05

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--