

## Wiha Soft Grip Pliers & Cutters



### Standard Adjustable Pliers



[SHOP](#)

#### 326 Adjustable Pliers - Box Type DIN ISO 5745

10 different opening sizes provide optimal adjustment to objects being gripped. Long durability achieved through additional induction hardening of jaws to approx. 58-60 HRC. Chrome-vanadium tool steel, hardened and tempered. Soft vinyl grips are oil and solvent resistant.

Item	↔	↔	Capacities			
No.	mm	Inch	Round	Hex	Pkg.	Lbs.
32660	180	7.0	1.25	1 1/2	1	.35
32661	250	10.0	1.75	2.0	1	.67
32663	300	12.0	2.0	2 1/4	1	1.17



### Slide Lock Adjustable Pliers - "QuickFix"



[SHOP](#)

#### 32668 Slide Lock Adjustable Pliers - Wiha QuickFix - Box Type

DIN ISO 8976 Super fast and easily adjusted pliers. Long durability achieved through additional induction hardening of jaws to approx. 56 HRC. Finger jam protection for safe operation in all settings. Chrome-vanadium tool steel, hardened and tempered. Soft vinyl grips.

Item	↔	↔	Capacities			
No.	mm	Inch	Round	Hex	Pkg.	Lbs.
32668	250	10.0	1 1/4	1 1/2	1	.72

- Open and slide to adjust opening size
- Audible click at each locking position
- Close to lock



### Rapid Adjustable - Push Button Pliers



[SHOP](#)

#### 326 Push Button Adjustable Water Pump Pliers - DIN ISO 8976

Extra narrow head for working in restricted spaces. Rapid and simple push button setting and locking. Long durability achieved by additional inductive hardening of gripper jaws to approx. 58-60 HRC. Finger jam protection in all settings ensures safe operation. Chrome-vanadium tool steel, hardened and tempered. Soft vinyl grips. For gripping and holding pipes and angular profiles such as hex nuts in the installation area.

Item	↔	↔	Capacities			
No.	mm	Inch	Round	Hex	Pkg.	Lbs.
32664	180	7.0	1.25	1 1/2	1	.35
32665	250	10.0	1.75	2.0	1	.80
32667	300	12.0	2.0	2 1/4	1	1.21

- Fast push button jaw release
- Finger jam protection in all settings



[SHOP](#)

#### 32669 3 Piece Push Button Set

Drop-forged from special tool steel, individually high frequency induction hardened. Precision formed. Soft vinyl grips, oil & solvent resistant.

Item# 32669 Set Includes:  Lbs. 2.50

32664 - Push Button Adjustable Water Pump Pliers - 7.0"

32665 - Push Button Adjustable Water Pump Pliers - 10.0"

32667 - Push Button Adjustable Water Pump Pliers - 12.0"



[SHOP](#)

#### 32670 3 Piece Adjustable Pliers Set

Drop-forged from special tool steel, individually high frequency induction hardened. Precision formed. Soft vinyl grips, oil & solvent resistant.

Item# 32670 Set Includes:  Lbs. 2.52

32660 - Adjustable Pliers, Box Type - 7.0"

32661 - Adjustable Pliers, Box Type - 10.0"

32663 - Adjustable Pliers, Box Type - 12.0"