

Wiha Soft Grip Pliers & Cutters

Retaining Ring Pliers - Internal



326 Straight Internal Retaining Ring Pliers DIN ISO 5256

Shape C, straight tips. Die forged cylindrical precision formed. Chrome-vanadium special tool steel. For inserting & removing internal retaining rings.

Item	↔	↔	⊙	⊙	● Tip	⊞	↔
No.	mm	Inch	Inch	mm	Inch/mm	Pkg.	lbs.
32681	139	5.5	5/16-1/2	8-13	.035/.9	1	.27
32682	140	5.5	1/2-1	12-25	.050/1.3	1	.27
32683	180	7.0	3/4-2 3/8	19-60	.070/1.5	1	.42
32684	225	8.9	1 1/2-4	40-100	.090/2.3	1	.63
32654	310	12.2	3.5-5.5	85-140	.126/3.2	1	1.13

90° Angle Retaining Ring Pliers - Internal



326 90° Angle Internal Retaining Ring Pliers DIN ISO 5254

Shape D, 90° angled tips. Die forged cylindrical precision formed. CV Special tool steel. For inserting & removing internal retaining rings. Soft vinyl grips.

Item	↔	↔	⊙	⊙	● Tip	⊞	↔
No.	mm	Inch	Inch	mm	Inch/mm	Pkg.	lbs.
32685	139	5.5	5/16-1/2	8-13	.035/.9	1	.27
32686	140	5.5	1/2-1	12-25	.050/1.3	1	.27
32687	165	7.0	3/4-2 3/8	19-60	.070/1.5	1	.43
32688	225	8.9	1 1/2-4	40-100	.090/2.3	1	.62
32656	310	12.2	3.5-5.5	85-140	.126/3.2	1	1.14

Retaining Ring Pliers - External



326 Straight External Retaining Ring Pliers DIN ISO 5254

Shape A, straight tips. Die forged cylindrical precision formed. CV special tool steel. For fitting & removing external retaining rings. Soft vinyl grips.

Item	↔	↔	⊙	⊙	● Tip	⊞	↔
No.	mm	Inch	Inch	mm	Inch/mm	Pkg.	lbs.
32689	139	5.5	1/8-3/8	3-10	.035/.9	1	.28
32690	140	5.5	3/8-1	10-25	.050/1.3	1	.28
32691	180	7.0	3/4-2 3/8	19-60	.070/1.5	1	.45
32692	225	8.9	1 1/2-4	40-100	.090/2.3	1	.62
32662	310	12.2	3.5-5.5	85-140	.126/3.2	1	1.13

90° Angle Retaining Ring Pliers - External



326 90° Angled External Retaining Ring Pliers DIN ISO 5254

Shape B, 90° angled tips. Die forged cylindrical precision formed. CV special tool steel. For fitting & removing external retaining rings. Soft vinyl grips.

Item	↔	↔	⊙	⊙	● Tip	⊞	↔
No.	mm	Inch	Inch	mm	Inch/mm	Pkg.	lbs.
32694	139	5.5	1/8-3/8	3-10	.035/.9	1	.28
32695	140	5.5	3/8-1	10-25	.050/1.3	1	.28
32696	180	7.0	3/4-2 3/8	19-60	.070/1.5	1	.44
32697	225	8.9	1 1/2-4	40-100	.090/2.3	1	.63
32666	310	12.2	3.5-5.5	85-140	.126/3.2	1	1.16