

Wiha MagicTip Safety Ring Pliers

Patents Pending



High performance precision notched tips for maximum stability & secure holding
 (Safety notched on .070, .090 & .126)



Hardened MagicTips are notched to hold rings securely on .070, .090 & .126 sizes

Tips made of premium quality hardened CVM tool steel, HRC 64

Heavy duty forged pliers with soft vinyl grips

- Faster & Easier Application
- Fewer Lost Rings
- Safer To Use
- Saves Time & Money



MagicTip Safety Ring Pliers-Internal



346 MagicTip Straight Internal Safety Ring Pliers DIN ISO 5256

Shape C, straight tips. Precision machined tips of Chrome-vanadium special tool steel. For inserting & removing internal retaining rings.

Item No.	mm	Inch	Inch	mm	Inch/mm	Pkg.	lbs.
34610	180	7.1	3/4-2 3/8	19-60	.070/1.5	1	.34
34611	220	8.7	1 1/2-4	40-100	.090/2.3	1	.54
34612	305	12.0	3.5-5.5	85-140	.126/3.2	1	.90

MagicTip 90° Angle Safety Ring Pliers - Internal



346 MagicTip 90° Angle Internal Safety Ring Pliers DIN ISO 5254

Shape D, 90° angled tips. Precision machined tips of Chrome-vanadium Special tool steel. For inserting & removing internal retaining rings. Soft vinyl grips.

Item No.	mm	Inch	Inch	mm	Inch/mm	Pkg.	lbs.
34615	180	7.1	3/4-2 3/8	19-60	.070/1.5	1	.34
34616	220	8.7	1 1/2-4	40-100	.090/2.3	1	.54
34617	305	12.0	3.5-5.5	85-140	.126/3.2	1	.94

No Dropped Rings!



Hardened MagicTips are notched to hold rings securely on .070, .090 & .126 sizes

Safety Notched "MagicTips"

Precision Machined To Hold Rings Securely

Saves Time & Money

Improves Productivity