






4 PIN 6 SOCKET
9520-981680




6 PIN 4 SOCKET
9520-981681



4 PIN 6 SOCKET
9520-981680

AS-016

6 PIN 4 SOCKET
9520-981681



HPHT
PRESSURE: 20,000 psi
TEMP: 200 °C
VOLTAGE: 500 V
INSULATION R: 500 MΩ

MPHT
PRESSURE: 10,000 psi
TEMP: 200 °C
VOLTAGE: 500 V
INSULATION R: 500 MΩ

REVISION			
REV	DESCRIPTION	DATE	APPROVED BY
A1	OPERATING LIMITS ADDED/TEMPLATE CHANGE	03-03-25	IC
A	INITIAL RELEASE	04-11-18	MB

PROPRIETARY AND CONFIDENTIAL
The information contained in this drawing is the sole property of Winchester Interconnect and shall not be used or disclosed without the prior written permission of Winchester Interconnect. Any reproduction in part or as a whole without written permission of Winchester Interconnect is prohibited.
www.winconn.com

DRAWN BY	MT	03-03-25
VERIFIED BY	DH	03-03-25
APPROVED BY	IC	03-03-25

DIMENSIONS ARE INCHES
TOLERANCES:
DECIMAL: .X ±.13
.XXX ±.063
ANGLES: ± 10°

FRACTION:
<120:0/+2
120 TO 1200:0/+4
>1200:±6
SCALE: NTS

Cadillac Win
Ruggedized Group
Houston, Texas



Winchester
Interconnect.
We Energize Innovation.

BULKHEAD CONNECTORS
9520-981680 4 PIN 6 SOCKET
9520-981681 6 PIN 4 SOCKET

SIZE A	9520-981680 9520-981681 SPEC	Rev. A1
-----------	------------------------------	------------

CAD FILE NO : 9520-981680 9520-981681 SPEC