


NOTES: UNLESS OTHERWISE SPECIFIED
 1. MATERIAL SPECIFICATIONS:
 RUBBER, BUNA N, 65-75 DUROMETER, COLOR: BLACK

REV	DESCRIPTION	BY DATE	APPD
01	PRELIMINARY DRAWING ER062731	CY 04/20/16	JB



CATALOG P/N: 99-1400

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: .XX [X.X] ± .01 [0.3] .XXX [X.XX] ± .005 [0.13] .XXXX [X.XXX] ± .XXXX ANGLES: ± 2° SCALE: 3:1				KINGS® WINCHESTER ELECTRONICS Winchester Electronics Corporation 199 Park Road Ext Suite 104 Middlebury, Connecticut 06762			
CUSTOMER SALES DRAWING				STRAIN RELIEF BOOT			
DRAWN CY	DATE 04/20/2016	APPROVED	DATE	A			
APPROVED XXX	DATE XX/XX/XX	APPROVED XXX	DATE XX/XX/XX				
SD99-1400				SHT 1	OF 1	REV 01	