


REVISIONS
CHANGES
CN 27545 C
SD 8 NOV 85

5



NOTES:

1. FOR USE WITH 174, 179, 187, 188, RAYCHEM 5024A-1312, 5026A-1018 & 5026A-1318 CABLE GROUPS.

HEX SIZES (ACROSS FLATS)					DIE WIDTH	WEB WIDTH		
A	B	C	D		F	G	H	I
.069		—	.125	—	.375	.080		—

UNLESS OTHERWISE SPECIFIED

1. TOLERANCES: DIMENSIONS & PLACES DIM. MAX. MIN. 2. REALIZE ALL BURNS, BREAK SHARP EDGES, OOS MAX
3. PLACE DIMENSIONS IN INCHES. 4. NO FILLETS PERMITTED
5. R. DIM. CONTINUED FOR ANY 2 DIM. FOR MAX. 6. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX
7. TO HOLD THE MAX. DIM. DIMENSIONS. 8. ALL DIMENSIONS PRIOR TO PLATING.

REF

FINISH

SPEC

MATH.

0 1 2 3 4

CRIMP DIE

DRAWN: HDE	DATE: 21 NOV 72
APP'D: LI	DATE: 21 NOV 72

KINGS ELECTRONICS
10 MARBLEDALE ROAD
TULSA, OKLA. 74106

KTH-2011