





NOTES:
1. FOR USE WITH RG-198/U CABLE.
2. FOR CABLING INSTRUCTIONS SEE CP-1012.

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES:
FRACTIONS $\pm .010$ DECIMALS $\pm .004$ ANGLES $\pm 0^\circ 30'$
T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT
EXCEED THE SUM OF THEIR TOLERANCES.
2. REMOVE ALL BURRS. BREAK SHARP EDGES .003 MAX.
3. NO FILLETS PERMITTED.
4. SURFACE ROUGHNESS 100 MICROINCHES RMS MAX.
5. ALL DIMENSIONS PRIOR TO PLATING.

ITEM	QTY	DESCRIPTION	DRAWING NO.
13	1	BODY	
12	1	BNC CONTACT F	1-544-4-M07
11	1	INSULATOR	
10	1	INSULATOR	C-19-110-3-M99
9	1	BUSHING	
8	1	HEX NUT	492A-9-MC7
7	1	LOCKWASHER	492A-12-MC7
6	1	BRAID CLAMP	C-19-110-2-MC7
5	1	GASKET	C-19-47-2-M99
4	1	GASKET	492A-10-M99
2	1	WASHER	C-19-37-6-MC7
1	1	CLAMP NUT	C-19-110-1-MC7

REVISIONS	
ISSUE	CHANGED
1	CN 6185A J.M. 23 JULY 68
2	CN 8553C J.M. 14 MAY 70
3	CN 12580A J.M. 10 AUG 73
4	CN 25264C GL 11 MAY 83

REVISIONS	
ISSUE	CHANGED
1	CN 6185A J.M. 23 JULY 68
2	CN 8553C J.M. 14 MAY 70
3	CN 12580A J.M. 10 AUG 73
4	CN 25264C GL 11 MAY 83

KINGS ELECTRONICS
40 MARLBOROUGH ROAD
TUCKAHOE, N. Y.
KC-19-110