



Specifications

- Insulation Resistance – 100MΩmin. @80VDC
- Withstanding Voltage – 80Vrms.min
- Differential Impedance – 100+/- 10Ω
- Operating Temperature – (-55°C to + 105°C)
- Mating Cycles – 200 times




Part Number (Details)

CN084-680-1232-1010-0



Variations



	Product name		MCH Module Type
1	CN084-680 -1232-1010-0		Full Height Four Tongue MCH MCH-1 + MCH-2 + MCH-3 + MCH-2
2	CN084-680 -1332-1110-0		Full Height Four Tongue MCH MCH-1 + MCH-3 + MCH-3 + MCH-2
3	CN084-680 -1432-1010-0		Full Height Four Tongue MCH MCH-1 + MCH-4 + MCH-3 + MCH-2
4	CN084-340 -1200-1000-0		Full Height and Half Height Two Tongue MCH MCH-1 + MCH-2
5	CN084-340 -0032-0010-0		Full Height and Half Height Two Tongue MCH MCH-3 + MCH-2
6	CN084-170 -1000-1000-0		Full Height and Half Height Single Tongue MCH MCH-1
7	CN084-170 -0030-0010-0		Full Height and Half Height Single Tongue MCH MCH-3