




ESD Dust Covers

.050"



9 thru 100 Contacts

Rugged Metal
Low Profile Plastic

MD



MD025RS



EXAMPLE: MD025RS
MDXXXXX

SIZE: _____
R – RUGGED
L – LOW PROFILE
P – PLUG
S – RECEPTACLE

Material: Carbon filled polypropylene
Static Decay meets MIL-PRF-81705D
Surface Resistivity per ASTM D 257-99(2005): $<1.0 \times 10^{12}$ ohms/square

RUGGED PLASTIC

SIZE	CONTACT ROWS	DIMENSIONS									
		A		B		C		D		PART NUMBER	
		PLUG	RCPT	PLUG	RCPT	PLUG	RCPT	PLUG	RCPT	PLUG	RCPT
9	2	.176	.238	.298	.360	.195	.215	.475	.460	MD009RP	MD009RS
15								.625	.610	MD015RP	MD015RS
21								.775	.760	MD021RP	MD021RS
25								.875	.860	MD025RP	MD025RS
31								1.025	1.010	MD031RP	MD031RS
37								1.175	1.160	MD037RP	MD037RS
51								1.525	1.510	MD051RP-2	MD051RS-2
51	3	.219	.281	.340	.400	.195	.215	1.125	1.110	MD051RP	MD051RS
69								1.425	1.410	MD069RP	MD069RS
100								1.500	1.615	MD100RP	MD100RS

LOW PROFILE PLASTIC

SIZE	CONTACT ROWS	DIMENSIONS									
		A		B		C		D		PART NUMBER	
		PLUG	RCPT	PLUG	RCPT	PLUG	RCPT	PLUG	RCPT	PLUG	RCPT
9	2	.125	.205	.256	.315	.210	.195	.400	.430	MD009LP	MD009LS
15								.550	.580	MD015LP	MD015LS
21								.700	.730	MD021LP	MD021LS
25								.800	.830	MD025LP	MD025LS
31								.950	.980	MD031LP	MD031LS
37								1.100	1.130	MD037LP	MD037LS
51								1.050	1.080	MD051LP	MD051LS

Not for use on receptacles with grounding fingers