




ITEM #	PART #	QTY	DESCRIPTION	MATERIAL
1	AP-145-1M	1	SHELL ASS'Y	303 SS & NEOPRENE
2	AP-125-6	1	INSERT ASS'Y	DIALLYPHTHALATE, TYPE SDGF & GOLD PLATED BRASS
3	AP-105-5	1	STRAIN RELIEF	NYLON
4	AP-116-3	1	WASHER	RUBBER
5	AP-116-7	1	NUT ADAPTER	ALUMINUM ALLOY ANODIZED
6	SEE TABLE #1	1	BUSHING	RUBBER
7	SEE TABLE #1	1	WASHER	STAINLESS STEEL
8	SEE TABLE #1	1	SPRING	302 STAINLESS STEEL
9	AP-116-6	1	STUD	ANODIZED, ALUMINUM ALLOY

NOTES:
1) UNLESS OTHERWISE SPECIFIED, THIS CONNECTOR MEETS ALL GENERAL REQUIREMENTS & SPECIFICATIONS OF MIL-C-55116
2) MATES WITH U-183/U PANEL MOUNT CONNECTOR & U-228/U INLINE CONNECTOR

C AP-125M-CP

TABLE #1				
PART #	CABLE SIZE	BUSHING	WASHER	SPRING
AP-125M-1	Ø .165± .010	AP-116-17	AP-116-2	AP-116-4
AP-125M-2	Ø .228± .010	AP-116-18	AP-116-2	AP-116-4
AP-125M-3	Ø .250± .010	AP-116-8	AP-116-2	AP-116-4
AP-125M-4	Ø .290± .010	AP-116-19	AP-116-2	AP-116-4
AP-125M-5	Ø .320± .010	AP-116-20	AP-116-22	AP-116-21



SECTION Y-Y
SCALE 3.000

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

					DWN.BY GPH		DATE 5/14/10		MATERIAL					
					CHECKED BY GPH		DATE 5/14/10		FINISH					
					APPR.BY GPH		DATE 5/14/10		WEIGHT		SCALE = 1.00 :1			
									NEXUS STAMFORD,CONN					
					B		DEL: 36° ,ADD: 48° REF: 36°		226		8/24 2015		HR	
					A		NEW RELEASE				5/14 2010		GH	