



FOR REFERENCE ONLY

SPECIFICATIONS:

AC RATING: 10 AMPS @115VAC (RESISTIVE LOAD)
5 AMPS @115VAC (INDUCTIVE LOAD)
3 AMPS @115VAC (LAMP LOAD)
DC RATING: 10 AMPS @28VDC (RESISTIVE LOAD)
5 AMPS @28VDC (INDUCTIVE LOAD)
3 AMPS @28VDC (LAMP LOAD)
TYPE 7 CONTACT ARRANGEMENTS:
1/2 AMPERAGE LOADS SHOWN ABOVE
MECHANICAL LIFE: 500,000 CYCLES
ACTION: MOMENTARY SNAP OR PUSH PULL
OPERATING FORCE:
SERIES 20 & 30: 3 TO 5 POUNDS MOMENTARY
1/2 TO 2 POUNDS PUSH-PULL
SERIES 22 & 32: 2 TO 3 POUNDS MOMENTARY
WEIGHT: .050 POUNDS MAXIMUM
CASE: ALUMINUM ALLOY 2011-T3,
CLEAR ANODIZED IAW MIL-A-8625
PLUNGER: GLASS FILLED NYLON
BODY: DIALYL PHTHALATE IAW MIL-M-14
TERMINALS: THREADED #2-56 NC-2B



DESCRIPTION

DUSTPROOF "300 SERIES" MOMENTARY SWITCH
2 CIRCUIT (CAN BE JUMPERED FOR SPDT)
ADAPTER TYPE "G", COLOR BLACK
BUTTON #1, COLOR BLACK

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

ORDERING INFORMATION:

NX303GB1B-00	SWITCH ONLY
NX303GB1B-60	SWITCH, MOUNTING HARDWARE
NX303GB1B-62	SWITCH, MOUNTING HARDWARE, TERMINAL HARDWARE
NX303GB1B-00EU	SWITCH (ROHS) ONLY
NX303GB1B-60EU	SWITCH (ROHS), MOUNTING HARDWARE
NX303GB1B-62EU	SWITCH (ROHS), MOUNTING HARDWARE, TERMINAL HARDWARE

DWN. BY	EWT	DATE	9/11/07	MATERIAL	N/A
CHECKED BY		DATE		FINISH	N/A
APPR. BY		DATE		WEIGHT	—
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON .XX .XXX ANGLES — ±.003 ±.5°				SCALE	N/A
				TITLE	SWITCH 2-CIRCUIT MOMENTARY (MS25089-3G)
DO NOT SCALE DWG.				SHEET	1 OF 1

NEXUS STAMFORD, CONN	
SIZE	DWG. NO.
B	NX303GB1B-XX

A	CORRECTED CONTACT 3 & 4 POSITION		4/14/08	EWT
LET.	REVISION	CN #	DATE	CHK.



SW-200-23
TERMINAL
(4)




SW-200-25
#2 LOCKWASHER
(4)




SW-200-72
#2-56 SCREW
(4)

TERMINAL
HARDWARE



SW-200-34
5/8-24 NUT
(1)



SW-200-35
5/8 LOCKWASHER
(1)

MOUNTING
HARDWARE