





4		3			DESCRIPTION
ITEM #	PART #	NX301GB1R-00 QTY	NX301GB1R-60 QTY	NX301GB1R-61 QTY	
1	NX301GB1R	1	1	1	
2	SW-200-35	----	1	1	
3	SW-200-34	----	1	1	
4	SW-200-23	----	----	2	
5	SW-200-25	----	----	2	
6	SW-200-72	----	----	2	

NOTES:
1) DUSTPROOF "SERIES 30" MOMENTARY SWITCH
CONTACT ARRANGEMENT: SPNO - SINGLE POLE, NORMALLY OPEN
BUTTON #1, COLOR: RED
ADAPTER TYPE: "G"
2) "YYWW" IS THE DATE CODE

SPECIFICATIONS;
AC RATING: 10 A @115VAC (RESISTIVE LOAD)
5A @ 115VAC (INDUCTIVE LOAD)
3A @115VAC (LAMP LOAD)
DC RATING: 10A @ 28VDC (RESISTIVE LOAD)
5A @ 28VDC (INDUCTIVE LOAD)
3A @ 28VDC (LAMP LOAD)
MECHANICAL LIFE: 500,000 CYCLES
ACTION: MOMENTARY SNAP
OPERATING FORCE: 3-5 LBS MOMENTARY
WEIGHT: .05 LBS MAX
CASE: ALUMINUM ALLOY 2011-T3, CLEAR ANODIZED
IAW MIL-A-8525
PLUNGER: GLASS FILLED NYLON
BODY: DIALLY PHTHALATE IAW MIL-M-14
TERMINALS: THREADED #2-56 NC-28



B NX301GB1R-XX



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

A	INITIAL RELEASE		4/17 2016	HR	
LET.	REVISION	CN #	DATE	CHK.	

DWN.BY HR	DATE 4/17/16	MATERIAL			
CHECKED BY	DATE	FINISH			
APPR.BY	DATE	WEIGHT —	SCALE = 1.00 :1		NEXUS STAMFORD,CONN
UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES &/OR [mm] TOLERANCES: DECIMAL: .XX[X.X] .XXX[X.XX] ± .0X[0.X] ± .00X[0.0X] FRACTION: X/X X/XX ANGLES: .X ± .X°		TITLE SWITCH SPNO MOMENTARY			
		DO NOT SCALE DWG.	SHEET 1 OF 1		
		SIZE B	DWG. NO. NX301GB1R-XX		