







REV.	DATE	DESCRIPTION
NC	12/27/03	INITIAL RELEASE



RECOMMENDED CABLE STRIPPING DIMENSIONS



- NOTE:
1. CRIMPED FERRULE
 2. CRIMPED CONTACT PIN
 3. MAX. PANEL THICKNESS = 6.5mm

8	HEX NUT	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	PART DESCRIPTION
7	LOCK WASHER	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:	DRAWN	G.R.S.	12/27/03
6	FERRULE	BRASS	NICKEL	1	0.5 - 8mm ± 0.20mm	CHECKED		
5	SLEEVE	DELRI	NATURAL	1	8 - 30mm ± 0.40mm	ISSUED		
4	GASKET	RUBBER	RED	1	30 - 120mm ± 0.50mm	SHEET	1 OF 1	
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:	PART NO.		
2	INSULATOR	TEFLON	NATURAL	1	.020 - .315 = ± 0.007"			
1	BODY	BRASS	NICKEL	1	.315 - 1.180 = ± 0.015"			
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/112/112719.DWG	DWG. NO. 112719.DWG
						REV. NC	SIZE A	SCALE NA

Amphenol Connex

BNC BULKHEAD CRIMP JACK (FOR RG-174/U, 188A/U, 316/U CABLE)

112719