


REV.	DATE	DESCRIPTION
NC	11/19/99	INITIAL RELEASE



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		APPROVALS	DATE	 Connex Connector Corporation TITLE MINI-UHF BULKHEAD CRIMP JACK (FOR 174/U, 188/U, 316/U CABLE)									
1	BODY	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	DRAWN	G.R.S.	11/19/99	SIZE A			FSM NO. 99001		DWG. NO. 182317.DWG		REV. NC	
2	INSULATOR	TEFLON	NATURAL		CHECKED											
3	BARREL	BRASS	NICKEL		ISSUED											
4	CONTACT PIN	PHOS. BRONZE	GOLD													
5	SLEEVE	DELIRIN	NATURAL													
6	FERRULE	BRASS	NICKEL													
7																
8					DO NOT SCALE DRAWING				SCALE	NA	PART NO.	182317	SHEET	1	OF	1