





REV.	DATE	DESCRIPTION
NC	04/16/98	INITIAL RELEASE



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		APPROVALS		DATE	TITLE (FOR BELDEN 8214, 9913) LMR 400 CABLE TNC CRIMP JACK Connector Corporation				
1 BODY	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	DO NOT SCALE DRAWING	DRAWN	G.R.S.	04/16/98	connector Corporation				
2 INSULATOR	TEFLON	NATURAL			CHECKED							
3 CONTACT PIN	PHOS. BRONZE	GOLD			ISSUED							
4 FERRULE	JIS	NICKEL										
5												
6												
7												
8												
							SCALE	NA	PART NO.	122392	SHEET	1