




REV.	DATE	ECR NO.	DESCRIPTION
NC	10/14/01	—	INITIAL RELEASE
A	03/26/09	100088	ADD TOLERANCES TO MOUNT HOLE DIMENSIONS



RECOMMENDED
MOUNTING HOLE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex									
						DRAWN	GRS	03/26/09											
6	HEX NUT	BRASS	NICKEL	1		CHECKED				PART DESCRIPTION SMA FEMALE TO TNC BULKHEAD FEMALE ADAPTER									
5	LOCK WASHER	PHOS. BRONZE	NICKEL	1		ISSUED													
4	GASKET	SILICONE	RED	1		SHEET	1 OF 1					PART NO. 242178							
3	CONTACT PIN	BER. COPPER	GOLD	1															
2	INSULATOR	PTFE	NATURAL	1	CAD FILE C:/242/242178.DWG					DWG. NO.		242178.DWG		REV.	A	SIZE	A	SCALE	NA
1	BODY	BRASS	NICKEL	1															
	DESCRIPTION	MATERIAL	FINISH	QTY															