


1. RECOMMENDED SOLDER: SN60 SOLDER PER FED SPEC QQ-5-571 AND A NON-HALIDE FLUX SIMILAR TO KESTER 197 OR EQUIVALENT.
2. SOLDERABLE AREA.
3. CAPACITANCE: 800pF MIN.
VOLTAGE: 50VDC MAX.
CURRENT: 10 AMPS MAX.
TEMPERATURE: -25°C TO +85°C
4. 0.51 [.020] MAX SWAGED METAL MATERIAL MAY INCREASE THE 0.81 [.032] DIA BY 1.02 [.040] MAX IN THIS AREA ONLY.
5. MATERIAL: BODY: EPOXY
PIN: COPPER
GROUND PIN: COPPER ALLOY
6. FINISH : PIN: SILVER
GROUND PIN: SILVER

[illegible][illegible]