





MECHANICALS



SCHEMATIC



MODEL / ITEM	RPC1299-30 / 1000-452	
UNITS	MM	
DATE	090709	
HOUSING	NYLON FR50	
MAX VOLT / CURR	75VDC / 30ADC	
FREQ(KHZ)		
AMB / STORAGE	40C / -40 TO 100C	
WT(LB/KG), TYP	0.2/0.09	RP RADIUS POWER AN AstrodyneTDI COMPANY
HIPOT,LG (VDC)	2.5K	
TYP LK CURR		
ANGLE=±0.5°	0.0/0.00=±0.5/±0.25	CONFIDENTIAL DOCUMENT