

SC Series

Sleeve Caps for Tube Ends



SC Series sleeve caps are designed to fit outside diameters of tubing with a snug friction grip. SC Series is ideal for capping and protecting both threaded and non-threaded tubing and rod ends. They also make excellent masks for painting, plating or grit-blasting operations.

- Available in over 60 different ODs and lengths

Material: Low-density polyethylene

Standard Color: Red

Item #	Dim A (IN)	Dim B (IN)		
SC-5/64	0.078	0.50	Available Options	Request Sample
SC-3/32	0.094	0.59	Available Options	Request Sample
SC-1/8	0.125	0.59	Available Options	Request Sample
SC-211-L	0.125	0.75	Available Options	Request Sample
SC-5/32	0.156	0.56	Available Options	Request Sample
SC-212-S	0.172	0.62	Available Options	Request Sample
SC-3/16-5	0.188	0.35	Available Options	Request Sample
SC-213-S	0.188	0.47	Available Options	Request Sample
SC-3/16-10	0.188	0.59	Available Options	Request Sample
SC-3/16-16	0.188	1.00	Available Options	Request Sample
SC-213-R	0.203	0.62	Available Options	Request Sample
SC-7/32	0.219	0.75	Available Options	Request Sample
SC-1/4-4	0.250	0.22	Available Options	Request Sample
SC-1/4-7	0.250	0.44	Available Options	Request Sample
SC-214-S	0.250	0.50	Available Options	Request Sample
SC-1/4-14	0.250	0.88	Available Options	Request Sample
SC-1/4-16	0.250	1.00	Available Options	Request Sample
SC-274-G	0.266	0.75	Available Options	Request Sample
SC-9/32	0.281	0.75	Available Options	Request Sample
SC-1805	0.313	0.38	Available Options	Request Sample
SC-5/16	0.313	0.88	Available Options	Request Sample
SC-216-T	0.375	0.46	Available Options	Request Sample
SC-155	0.375	0.75	Available Options	Request Sample
SC-3/8	0.375	0.88	Available Options	Request Sample
SC-216-L	0.375	1.12	Available Options	Request Sample
SC-1030	0.422	1.25	Available Options	Request Sample
SC-773	0.438	0.22	Available Options	Request Sample
SC-7/16-8	0.438	0.50	Available Options	Request Sample
SC-159	0.438	0.62	Available Options	Request Sample
SC-7/16-14	0.438	0.88	Available Options	Request Sample
SC-217-L	0.438	1.50	Available Options	Request Sample
SC-7/16-16	0.438	1.00	Available Options	Request Sample
SC-157	0.469	0.75	Available Options	Request Sample
SC-161	0.500	0.44	Available Options	Request Sample
SC-1/2-8	0.500	0.50	Available Options	Request Sample
SC-1/2-14	0.500	0.88	Available Options	Request Sample
SC-1/2-24	0.500	1.50	Available Options	Request Sample
SC-176	0.563	0.42	Available Options	Request Sample
SC-9/16-9	0.563	0.56	Available Options	Request Sample
SC-219-S	0.563	0.62	Available Options	Request Sample
SC-9/16-14	0.563	0.88	Available Options	Request Sample
SC-1868	0.625	0.64	Available Options	Request Sample
SC-5/8	0.625	0.88	Available Options	Request Sample
SC-981	0.625	0.88	Available Options	Request Sample
SC-220-H	0.625	0.94	Available Options	Request Sample
SC-220-U	0.625	1.50	Available Options	Request Sample
SC-1834	0.625	2.50	Available Options	Request Sample
SC-221-S	0.688	0.75	Available Options	Request Sample
SC-11/16	0.688	0.88	Available Options	Request Sample
SC-1775	0.740	0.88	Available Options	Request Sample
SC-222-S	0.750	0.38	Available Options	Request Sample
SC-3/4	0.750	0.88	Available Options	Request Sample
SC-3/4-16	0.742	1.00	Available Options	Request Sample
SC-222-H	0.750	0.94	Available Options	Request Sample
SC-222-L	0.750	2.47	Available Options	Request Sample
SC-25/32	0.781	1.00	Available Options	Request Sample
SC-835	0.813	0.69	Available Options	Request Sample
SC-13/16	0.813	0.88	Available Options	Request Sample
SC-201-T	0.875	0.62	Available Options	Request Sample
SC-201-S	0.875	0.62	Available Options	Request Sample
SC-7/8	0.875	0.88	Available Options	Request Sample
SC-201-M	0.875	1.75	Available Options	Request Sample
SC-748	0.906	0.75	Available Options	Request Sample
SC-1202	0.906	0.88	Available Options	Request Sample
SC-15/16	0.938	1.00	Available Options	Request Sample
SC-15/16-23	0.940	1.45	Available Options	Request Sample
SC-1784	1.000	0.50	Available Options	Request Sample
SC-2003	1.000	0.50	Available Options	Request Sample
SC-1364	1.000	0.62	Available Options	Request Sample
SC-138	1.000	0.75	Available Options	Request Sample
SC-1	1.000	1.00	Available Options	Request Sample
SC-138-L	1.000	1.75	Available Options	Request Sample
SC-1 1/16	1.063	1.00	Available Options	Request Sample
SC-224	1.125	0.88	Available Options	Request Sample
SC-1 1/8	1.125	1.00	Available Options	Request Sample
SC-1 1/8-21	1.125	1.31	Available Options	Request Sample
SC-1 3/16	1.188	1.00	Available Options	Request Sample
SC-289-S	1.250	0.50	Available Options	Request Sample
SC-1831	1.250	0.87	Available Options	Request Sample
SC-1 1/4	1.250	1.00	Available Options	Request Sample
SC-289-M	1.250	1.50	Available Options	Request Sample
SC-289-L	1.250	1.75	Available Options	Request Sample
SC-1 5/16-12	1.313	0.75	Available Options	Request Sample
SC-1 5/16	1.313	1.00	Available Options	Request Sample
SC-760	1.375	0.62	Available Options	Request Sample
SC-1 3/8	1.375	1.00	Available Options	Request Sample
SC-428	1.375	1.50	Available Options	Request Sample
SC-428-2	1.375	1.59	Available Options	Request Sample
SC-1975	1.500	0.87	Available Options	Request Sample
SC-1 1/2	1.500	1.00	Available Options	Request Sample
SC-290-L	1.500	1.75	Available Options	Request Sample
SC-1 5/8	1.625	1.00	Available Options	Request Sample
SC-291-L	1.625	1.25	Available Options	Request Sample
SC-291-2	1.719	1.00	Available Options	Request Sample
SC-1008	1.750	0.88	Available Options	Request Sample
SC-1 3/4	1.750	1.00	Available Options	Request Sample
SC-291-3	1.844	1.21	Available Options	Request Sample
SC-1 7/8	1.875	1.00	Available Options	Request Sample
SC-1 29/32	1.906	1.00	Available Options	Request Sample
SC-2	2.000	0.88	Available Options	Request Sample
SC-226	2.000	1.00	Available Options	Request Sample
SC-226-L	2.000	1.53	Available Options	Request Sample
SC-1025	2.125	0.50	Available Options	Request Sample
SC-2 1/8	2.125	1.00	Available Options	Request Sample
SC-2 1/4	2.250	0.88	Available Options	Request Sample
SC-1365	2.250	1.00	Available Options	Request Sample
SC-2 3/8	2.375	0.88	Available Options	Request Sample
SC-2 1/2	2.500	0.88	Available Options	Request Sample
SC-2 9/16	2.563	1.00	Available Options	Request Sample
SC-372	2.609	1.00	Available Options	Request Sample
SC-2 5/8	2.625	1.00	Available Options	Request Sample
SC-2 3/4	2.750	1.00	Available Options	Request Sample
SC-3	3.000	1.00	Available Options	Request Sample
SC-3 1/16	3.062	2.00	Available Options	Request Sample
SC-3 1/8	3.125	1.38	Available Options	Request Sample
SC-1528	3.250	1.00	Available Options	Request Sample
SC-3 5/16	3.313	1.00	Available Options	Request Sample
SC-1563	3.438	1.00	Available Options	Request Sample
SC-1521	3.500	1.00	Available Options	Request Sample
SC-3 1/2	3.500	1.38	Available Options	Request Sample
SC-2215	3.531	2.00	Available Options	Request Sample
SC-3 5/8	3.625	1.38	Available Options	Request Sample
SC-3 3/4	3.750	1.38	Available Options	Request Sample
SC-1540	4.000	1.13	Available Options	Request Sample
SC-4	4.000	1.38	Available Options	Request Sample
SC-4 1/8	4.125	1.50	Available Options	Request Sample
SC-4 1/2	4.500	1.44	Available Options	Request Sample
SC-1400	4.813	0.64	Available Options	Request Sample
SC-1363	4.875	0.92	Available Options	Request Sample
SC-5 1/8	5.125	1.63	Available Options	Request Sample
SC-5 1/4	5.250	1.80	Available Options	Request Sample
SC-324-3	8.000	2.30	Available Options	Request Sample