






147 Central Avenue
Hackensack, New Jersey 07601
Tel: 201-489-8989 • Fax: 201-489-6911



CHICAGO MINIATURE LAMP, INC.
WHERE INNOVATION COMES TO LIGHT

Electrical Industry Lamps

T-6		Part Number	Operating Voltage	Design Watts	Initial MSC P	Average Life Hours	M.O.L. (inches)	Base
		15T6/60V	60	15.0	9.5	2,000	3.062	Candelabra Screw
		15T6/120V	115-125	15.0	9.1	2,000	3.062	Candelabra Screw
		15T6DC/120V	115-125	15.0	9.1	2,000	3.062	Double Contact Bayonet
		15T6/145V	140-150	15.0	9.4	2,000	3.062	Candelabra Screw
T-6 1/2		20T6-1/2N/120V	120	20.0	7.2	-	5.500	Intermediate Base
		20T6-1/2DC/120V	120	20.0	7.2	-	5.500	Double Contact Bayonet
		25T6-1/2N/120V	115-125	25.0	20.0	1,000	5.500	Intermediate Base
C-7		4C7/120V	115-125	4.0	1.3	3,000	2.125	Candelabra Screw
		7C7/120V	115-125	7.0	3.6	3,000	2.125	Candelabra Screw
		7C7DC/120V	115-125	7.0	3.6	3,000	2.125	Double Contact Bayonet
		10C7/120V	115-125	10.0	4.5	1,500	2.125	Candelabra Screw
		10C7DC/120V	115-125	10.0	4.5	1,500	2.187	Double Contact Bayonet
T-7		15T7/120V	115-125	15.0	9.1	2,000	2.250	Candelabra Screw
		15T7N/120V	115-125	15.0	9.1	2,000	2.250	Intermediate Base
		15T7DC/120V	115-125	15.0	9.1	2,000	2.250	Double Contact Bayonet
		20T7N/120V	115-125	20.0	8.0	2,000	2.250	Intermediate S crew
		30T7N/120V	115-125	20.0	10.0	2,000	2.250	Intermediate S crew
T-8		15T8/120V	115-125	15.0	11.9	1,000	2.625	Candelabra Screw
		15T8N/120V	115-125	15.0	11.9	1,000	2.625	Intermediate S crew
		25T8/120V	115-125	25.0	18.7	1,000	2.625	Candelabra Screw
		25T8N/120V	115-125	25.0	18.7	1,000	2.625	Intermediate S crew
		25T8DC/120V	115-125	25.0	18.7	1,000	2.625	Double Contact Bayonet
		25T8DC/130V	130	25.0	18.7	1,000	2.625	Double Contact Bayonet
		25T8N/230V	230	25.0	16.8	-	2.625	Intermediate S crew
		25T8DC/230V	230	25.0	16.8	-	2.625	Double Contact Bayonet

Chicago Miniature Lamp reserves the right to make specification revisions that enhance the design and/or performance of the product