


TYPE B/2

Female connector – straight and angled – 16 and 32 positions




RoHS compliant

DESCRIPTION

- Solder pin, solder lug and wire wrap
- Quality class 3 (also available in quality class 2 or 1)
- Special assembly on request

PRODUCT DRAWING



ORDER DATA

(Dim. = mm)

No. of Pos.	Row	• = contact, + = no contact					Wire Wrap	Solder pin straight 2.5 mm	Solder pin straight 4 mm	Solder lug	Solder pin angled	Solder pin straight 2.5 mm with clip
		Pos.	1	2	3	4	5	...				
16	a		•	•	•	•	•		122 A 10419 X	122 A 10449 X	122 A 10479 X	122 A 10509 X
	b		+	+	+	+	+	+		122 A 10539 X	122 A 13219 X	
16	a		+	•	+	•	+	•	122 A 10429 X	122 A 10459 X	122 A 10489 X	122 A 10519 X
	b		+	•	+	•	+	•	122 A 10489 X	122 A 10519 X	122 A 10549 X	122 A 13229 X
32	a		•	•	•	•	•	•	122 A 10439 X	122 A 10469 X	122 A 10499 X	122 A 10529 X
	b		•	•	•	•	•	•	122 A 10499 X	122 A 10529 X	122 A 10559 X	122 A 13239 X

Clip for hole diameter 2.8 ± 0.1 mm, PCB thickness = 1.6 mm