






CONTACT PLATING	PART-NO.
SIGNAL CONTACTS GOLD FLASH over NICKEL	3H15W4PAM99A10X
SIGNAL CONTACTS 30µin HARD GOLD over 50µin NICKEL	3H15W4PCM99A10X



NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: SEE TABLE
SOLDER CUP ACCEPTS CABLE AWG 22
- NO CONTACTS ON POS. A1 - A4
- CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND					tolerance		 dim. in mm	scale: 2:1 (5:1)		
								material: SEE NOTES		
					date	name	title: D-SUB HD COMBINATION MALE 15W4P SOLDER CUP			
					drawn 13.03.2013	Liedmann				
					appd. 13.03.2013	Koch				
					norm					
					d-old		dwg no:		DIN-A3	
								13K1A4238		sh: 1
	a	Original						part no: SEE TABLE		
	rev.	description	date	name						

CONEC