



**Directive 2002/95/EC
"RoHS"
Compliant**

(click on the schematic(s) for a more detailed view)



No. of pos.	A -0,76	B-0,25	C
15	31,19	16,46	25,00 ^{+0,12} _{-0,13}
26	39,52	24,79	33,30 ^{+0,15} _{-0,10}
44	53,42	38,50	47,04 ^{±0,13}
62	69,70	54,96	63,50 ^{±0,13}
78	67,31	52,55	61,10 ^{+0,14} _{-0,11}

Plug connector:

No. of pos.	A -0,76	B+0,25	C	D -0,30
15	31,19	16,79	25,00 ^{+0,12} _{-0,13}	6,12
26	39,52	25,12	33,30 ^{+0,15} _{-0,10}	6,12
44	53,42	38,84	47,04 ^{±0,13}	5,99
62	69,70	55,30	63,50 ^{±0,13}	5,99
78	67,31	52,68	61,10 ^{+0,14} _{-0,11}	5,99

Part Numbers

No.of Pos.	Socket connector tin-plated	
	RoHS Compliant	RoHS Compliant
15	302 A 10869 X	DLH1XS8AK42X
26	302 A 10879 X	DLH2XS8AK42X
44	302 A 10889 X	DLH3XS8AK42X
62	302 A 10899 X	DLH4XS8AK42X
78	302 A 11629 X	DLH5XS8AK42X

No.of Pos.	Plug connector tin-plated with ground indent	
	RoHS Compliant	RoHS Compliant
15	301 A 10869 X	DLH1XP8AK42X
26	301 A 10879 X	DLH2XP8AK42X
44	301 A 10889 X	DLH3XP8AK42X
62	301 A 10899 X	DLH4XP8AK42X
78	301 A 11369 X	DLH5XP8AK42X

